


SAKDU 16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Feed-through terminal, Screw connection, 10 mm ² , 800 V, 76 A, grey
Order No.	1256770000
Type	SAKDU 16
GTIN (EAN)	4050118120509
Qty.	50 items

SAKDU 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

Dimensions and weights

Depth	49.75 mm	Depth (inches)	1.9587 inch
Depth including DIN rail	50.5 mm	Height	51 mm
Height (inches)	2.0079 inch	Width	12 mm
Width (inches)	0.4724 inch	Net weight	21.96 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66/6	Colour	grey
UL 94 flammability rating	V-0		

System specifications

End cover plate required	Yes	Number of potentials	1
Number of levels	1	Number of clamping points per level	2
Mounting rail	TS 35		

Additional technical data

Explosion-tested version	No	Type of mounting	Snap-on
--------------------------	----	------------------	---------

Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

Conductors for clamping (rated connection)

Gauge to IEC 60947-1	B6	Wire connection cross section AWG, max.	AWG 4
Connection direction	on side	Tightening torque, max.	1.6 Nm
Tightening torque, min.	1.2 Nm	Stripping length	15.5 mm
Type of connection	Screw connection	Number of connections	2
Clamping range, max.	16 mm ²	Clamping range, min.	2.5 mm ²
Clamping screw	M 4	Wire connection cross section AWG, min.	AWG 12

SAKDU 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	16 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	4 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	16 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	4 mm ²
Wire connection cross section, finely stranded, max.	16 mm ²	Wire connection cross section, finely stranded, min.	4 mm ²
Connection cross-section, stranded, max.	16 mm ²	Connection cross-section, stranded, min.	2.5 mm ²
Wire connection cross-section, solid core, max.	16 mm ²	Wire connection cross-section, solid core, min.	2.5 mm ²

General

Wire connection cross section AWG, max.	AWG 4	Wire connection cross section AWG, min.	AWG 12
Mounting rail	TS 35		

Rating data

Rated cross-section	10 mm ²	Rated voltage	800 V
Rated DC voltage	800 V	Nominal current	76 A
Current at maximum wires	76 A	Volume resistance according to IEC 60947-7-x	0.56 mΩ
Rated impulse withstand voltage	8 kV	Power loss in accordance with IEC 60947-7-x	1.82 W
Surge voltage category	III	Pollution severity	3

UL rating data

Voltage size B (UR)	600 V	Current size B (UR)	85 A
Conductor size Factory wiring max. (UR)	4 AWG	Current size C (UR)	85 A
Voltage size C (UR)	600 V	Conductor size Factory wiring min. (UR)	12 AWG
Certificate No. (UR)	E60693	Conductor size Field wiring min. (UR)	12 AWG
Conductor size Field wiring max. (UR)	4 AWG		

Classifications

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-01
ECLASS 15.0	27-25-01-01		

SAKDU 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Accessories

General ordering data

Type	SAKQ 16/2	Version
Order No.	1257090000	Cross-connector (terminal), grey
GTIN (EAN)	4050118120677	
Qty.	20 ST	
Type	SAKQ 16/3	Version
Order No.	1257110000	Cross-connector (terminal), grey
GTIN (EAN)	4050118120684	
Qty.	20 ST	
Type	SAKQ 16/4	Version
Order No.	1257120000	Cross-connector (terminal), grey
GTIN (EAN)	4050118120691	
Qty.	20 ST	
Type	SAKQ 16/10	Version
Order No.	1257130000	Cross-connector (terminal), grey
GTIN (EAN)	4050118120707	
Qty.	20 ST	
Type	SAKAP 16	Version
Order No.	1257070000	End and partition plate for terminals, grey, Height: 50 mm, Width: 1.5 mm, V-O, PA 66/6
GTIN (EAN)	4050118120615	
Qty.	20 ST	
Type	SAKAP 16 BL	Version
Order No.	1370370000	End and partition plate for terminals, blue, Height: 50 mm, Width: 1.5 mm, V-O, PA 66/6
GTIN (EAN)	4050118178739	
Qty.	20 ST	
Type	SAKEW 35	Version
Order No.	1129450000	End and partition plate for terminals, grey, Height: 50 mm, Width: 8.5 mm, V-O, PA 66/6
GTIN (EAN)	4032248970612	
Qty.	50 ST	
Type	SAKTW 35	Version
Order No.	2696960000	End and partition plate for terminals, grey, Height: 55 mm, Width: 1.5 mm, V-O, PA 66/6
GTIN (EAN)	4050118861464	
Qty.	20 ST	

SAKDU 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

Type	SDS 1.0X5.5X150	Version
Order No.	2749380000	Screwdriver, Blade width (B): 5.5 mm, Blade length: 150 mm, Blade thickness (A): 1 mm
GTIN (EAN)	4050118895605	
Qty.	1 ST	

Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
 - Strips for fast installation
 - Terminal markers, suitable for all Weidmüller cable connectors
 - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	DEK 5/8 PLUS MC NE WS	Version
Order No.	1046350000	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782055	Weidmueller, white
Qty.	800 ST	

BLM



SAKDU 16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****General ordering data**

Type	BLM 5/8 TB	Version	
Order No.	7760380692	BLM, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 Weidmueller,	
GTIN (EAN)	6944169819148	white	
Qty.	4800 ST		