

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PVC, yellow, Plug angled M8, on Socket angled M8, cable length: 0.5 m

Commercial data

Item number	1406207
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BF1
Product key	AF1IAB
GTIN	4046356798433
Weight per piece (including packing)	23.2 g
Weight per piece (excluding packing)	23 g
Customs tariff number	85444290
Country of origin	US

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard, U.S. cables
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	No

Connection data

Conductor connection

Tightening torque	0.2 Nm (M8 connectors)
-------------------	------------------------

Connector

Connection 1

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Type	Plug angled M8
Number of positions	4


Connection 2

Type	Socket angled M8
Number of positions	4

Cable/line

Cable length	0.5 m
--------------	-------

PVC yellow 105 °C [542]

Dimensional drawing	
Cable weight	25 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	4
Shielded	no
Cable type	PVC yellow 105 °C [542]
Conductor structure signal line	32x 1.10 mm
AWG signal line	24
Wire diameter incl. insulation	1.12 mm ±0.03 mm
External cable diameter	4.40 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black, white
Overall twist	4 wires, twisted
Max. conductor resistance	max. 79.7 Ω/km (20 °C)
Insulation resistance	≥ (550 M Ohms/m @ 500V)
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, movable installation	36 mm
Flame resistance	FT4
Other resistance	UV resistant
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable




1406207

<https://www.phoenixcontact.com/in/products/1406207>


Drawings

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

Circuit diagram




Contact assignment of M8 plugs/sockets

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable

1406207


<https://www.phoenixcontact.com/in/products/1406207>

Schematic diagram



Layout of connector pin assignments

Schematic diagram




Layout of connector pin assignments

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable

1406207


<https://www.phoenixcontact.com/in/products/1406207>

Dimensional drawing



Socket M8 x 1, angled

Schematic diagram




Pin assignment M8 socket, 4-pos., view female side

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable

1406207

<https://www.phoenixcontact.com/in/products/1406207>

Dimensional drawing



M8 x 1 male plug, angled version

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1406207>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387				
---	--	--	--	--

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	4 A	-	-

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	4 A	-	-

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	26980650-c52a-4d6d-8143-dc46b5e813d8

EF3.0 Climate Change

CO2e kg	0.218 kg CO2e
---------	---------------

SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

Accessories

PROT-M 8 FS-PA-CHAIN - Sealing cap

1430857

<https://www.phoenixcontact.com/in/products/1430857>

M8 sealing cap made of plastic with fixing band for sensor cables, for M8 plugs



PROT-M 8 MS-PA-CHAIN - Screw plug

1430860

<https://www.phoenixcontact.com/in/products/1430860>

M8 sealing cap made of plastic with fixing band for sensor cables, for M8 sockets



SAC-4P-M8MR/ 0,5-542/M8 FR BK - Sensor/actuator cable



1406207

<https://www.phoenixcontact.com/in/products/1406207>

TSD 02 SAC - Torque screwdriver

1208487

<https://www.phoenixcontact.com/in/products/1208487>



Torque screwdriver, with preset torque of 0.2 Nm and 4 mm hexagonal drive for M8 connectors

SAC BIT M8-D10 - Tool

1208461

<https://www.phoenixcontact.com/in/products/1208461>



Nut for assembling M8 connectors with longitudinal knurl and a knurl diameter of 10 mm, for 4 mm hexagonal drive

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in