




MARKING:



No	BOM ITEM	Q' TY	P/N
1	KWC-50T BLADE	2 pcs	BBN50T02
2	PVC 35P (SA93, SP-12N)	11.5 g	RPP03512
3	PE TIE (BLACK, 6 inch)	1 pcs	KBB10006



WIRING COLOR:

N: Stripe  
L: Non-Stripe

<p>LENGTH ON CORD: (604-14)</p> <p>(UL) E315167 SPT-2 105°C 2X18AWG(0.824mm<sup>2</sup>) 300V VW-1 I-SHENG CSA LL81924 TYPE SPT-2 105°C 2X0.824mm<sup>2</sup>(18AWG) 300V VW-1</p>
--

CABLE SPT-2 18AWGx2C 105°C DENT PRINT CT-12 (BLACK)				
PLUG SP-12N		LENGTH	2010	UNIT mm
CLIENT	NAME first connectivity		N/W	
	P/N 7316179	SG DWG	SR-141239-1	UNIT kg
			VER.	A
Design. by 賀艷紅 (2014.05.26)				
Review. by 朱曉玲 (2014.05.26)				
Approval. by 周德雲 (2014.01.16)				
A2N		2S2516	12	201 00