

Datasheet

RS Pro 15 Way Right Angle Through Hole Mount PCB D-sub Connector Socket, 2.77mm Pitch

RS Stock No: **528-3711**



Product Details

RS Pro D-sub connector socket comes with dimpled plug shells for reliable grounding. This right angle socket with 15 contacts has steel housing. The through hole PCB mount socket has 5 A current rating and 250 V ac voltage rating.

Features and Benefits

- Connectors with machined contacts
- 90° PCB plug and socket
- Copper alloy contacts with gold over nickel plating

**Specifications:**

Body Orientation	Right Angle
Contact Material	Copper Alloy
Contact Plating	Gold Over Nickel
Current Rating	5 A
Depth	12.55 mm
Dimensions	39.14 x 4.1 x 12.55 mm
Gender	Female
Housing Material	Steel
Length	39.14 mm
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Mounting Type	Through Hole
Number of Contacts	15
Pitch	2.77 mm
Voltage Rating	250 V ac
Width	4.1 mm