

PRODUCT-DETAILS

# GSC710

## TWO-PIECE OUTER SLV CONN BLUE RND



### General Information

Extended Product Type	GSC710
Product ID	7TAI029060R0021
EAN	5414363114918
Catalog Description	TWO-PIECE OUTER SLV CONN BLUE RND
Long Description	Two Piece Outer Sleeve Connector for Round Range, Length 15.2mm, Inner Diameter 18.03mm, Outer Diameter 20.07mm, Color Blue, Copper Alloy

### Ordering

EAN	5414363114918
UPC	786210814087

### Dimensions

Product Net Length	0, mm
--------------------	-------

### Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	3 in 76 mm
Package Level 1 Height	3.5 in 89 mm

Package Level 1 Depth / Length	3 in 76 mm
Package Level 2 Units	250 piece
Package Level 2 Width	3.12 in 79 mm
Package Level 2 Height	9.75 in 248 mm
Package Level 2 Depth / Length	7 in 178 mm

## Additional Information

Brand / Label	Sta-Kon
Color	Blue
Effective Date	19680424
Material	Copper
Number of Batteries	0
Product Name	COPPER GROUNDING RING
Product Type	Two-Piece Outer Sleeve Connector
Special Functions	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Circular Range (the corresponding outer sleeve is crimped with a hydraulic head and the result is a circular-shaped crimp), for grounding multiple or overall shielded cables. The sleeves are color coded according to their size. Applications in communications, aerospace, and electronics.

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GSC710
Instructions and Manuals	GSC710

## Classifications

ETIM 6	EC002650 - Connection for screened wires
ETIM 7	EC002650 - Connection for screened wires
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

