



ENGLISH

Datasheet

Stock No: 602-432

RS Pro 2265kgf Bench Mount Machine Press



Product Details

5000 lb Lever Press

Bench mounting press with a 12in (300 mm) throat depth and 5000 lbf ram pressure for increased scope in metal working and equipment fabrication. A chute for removing off-cuts, is supplied with the press, plus a bracket to hold the operating lever in a convenient rest position during tooling adjustments

Strong double frame construction made from flame cut steel

Hand operated lever transferring power to the ram via a rack & pinion mechanism

Ram limit stop determines cutting depth, safeguarding against tool & material damage

Includes fixing bolts, nuts & brackets for bench mounting



ENGLISH

| Dimensions (mm) | |
|------------------------------|---------------------|
| L. (overall) | 550 |
| H. max. (excl. lever) | 600 |
| W. (incl. mtg. brackets) | 197 |
| Handle Length | 762 |
| Throat Depth | 308 |
| Clearance | 127 |
| Stroke length (stop fitted) | 127 |
| Ram spigot hole dia. | 25 |
| Ram spigot hole depth | 30 |
| Base central hole dia. | 50.8 |
| Bench mounting. 4 holes f.c. | 225×166 by 10 clear |
| Press weight | 66 kg |

Specifications:

| | |
|-----------------|-------------|
| Type | Bench Mount |
| Output Pressure | 2265kgf |
| Model Number | 602-432 |