


Actuator

45-
2736.1960.000

Distribution by
Rs-online



<https://rs-online.eao.com/p/45-2736.1960.000>

Your product:



45-2736.1960.000 Actuator

FRONT

Front dimension:	Ø 40 mm
Front form:	Round
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	Blue
Lens material:	Plastic
Lens illumination:	Non illuminated
Lens shape:	Mushroom-head
Lens optics:	opaque

MECHANICAL CHARACTERISTIC

Switching action:	Maintained
Release type:	Twist to unlock
Mechanical lifetime:	300 000 cycles of operation
Operating frequency:	Max. 600/h

Weight: 0.046 kg

AMBIENT CONDITION

IP front protection: IP66, IP67, IP69K

Operating temperature: – 25 °C ... + 70 °C

Storage temperature: – 40 °C ... + 80 °C

Shock resistance: According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

Vibration resistance: According to IEC 60068-2-6: 20 ... 500 Hz: 5 g

Climate resistance: During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

Standards: IEC EN 60204-1

OTHER

Short Description: Actuator, Ø 22.3 mm, Ø 40 mm, Mushroom-head, Non illuminated, Blue, Plastic, opaque, Round, Black, Plastic, Maintained, IP66, IP67, IP69K, Twist to unlock


Dimension: Ø 40 mm

Housing material: Plastic


Product attributes: Twist to unlock clockwise

Hints: Application as per DIN EN ISO 13850 and EN 60204-1

Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

