

## Base strip - MCV 0,5/12-G-2,54 P20THRR56C2 - 1706157

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 12, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Mounting: Taped SMD/THT/THR components, Fixed coding of the last position, can be combined with the FMC 0,5/...-ST-2,54 C2 connector



The illustration shows the 10-position version



### Key commercial data

Packing unit	315 pc
Minimum order quantity	315 pc
GTIN	 4 046356 841955
Weight per Piece (excluding packing)	2220.0 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length	4.8 mm
Height	7.1 mm
Width	35.02 mm
Pitch	2.54 mm
Dimension a	27.94 mm
Pin dimensions	0,64 x 0,64 mm
Hole diameter	1.2 mm

#### General

Range of articles	MCV 0,5/...-G-THR
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV

## Base strip - MCV 0,5/12-G-2,54 P20THRR56C2 - 1706157

### Technical data

#### General

Rated voltage (III/3)	32 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE
Nominal current I <sub>N</sub>	6 A
Insulating material	LCP
Inflammability class according to UL 94	V0
Color	black
Number of positions	12

### Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

#### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

#### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

### Accessories

#### Accessories

Labeled terminal marker

## Base strip - MCV 0,5/12-G-2,54 P20THRR56C2 - 1706157

### Accessories

Marker card - SK 2,54/2,8:FORTL.ZAHLEN - 0804853



Marker card, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 99, Mounting type: Adhesive, for terminal block width: 2.54 mm, Lettering field: 2.54 x 2.8 mm

### Additional products


Printed-circuit board connector - FMC 0,5/12-ST-2,54 C2 - 1706232



Plug component, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 12, Pitch: 2.54 mm, Connection method: Spring-cage connection, Color: black, Contact surface: Gold, Fixed coding of last position; can be combined with MC(V) 0,5/...-G-2,54...C2 headers

### Drawings

Drilling diagram



Dimensioned drawing

