

SWITCHING ELEMENT, W. ONE CONTACT ELEMENT, 1NC,
PLUG-TYPE TERMINAL

Product designation	contact block
Contact block/ lampholder:	
Number of lampholders	0
General technical data:	
Product function	
<ul style="list-style-type: none"> • positive opening 	Yes
Suitability for integration	pushbutton / selector button
Protection class IP	
<ul style="list-style-type: none"> • of the enclosure 	IP40
<ul style="list-style-type: none"> • of the terminal 	IP20
Vibration resistance	
<ul style="list-style-type: none"> • acc. to IEC 60068-2-6 	20 ... 200 Hz: 5g
Equipment marking	
<ul style="list-style-type: none"> • acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750 	S
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 	S
<ul style="list-style-type: none"> • acc. to DIN EN 81346-2 	S
Auxiliary circuit:	
Number of NC contacts	
<ul style="list-style-type: none"> • for auxiliary contacts 	1
Number of NO contacts	
<ul style="list-style-type: none"> • for auxiliary contacts 	0
Number of CO contacts	
<ul style="list-style-type: none"> • for auxiliary contacts 	0
Operating current at AC-12	
<ul style="list-style-type: none"> • at 24 V rated value 	10 A
<ul style="list-style-type: none"> • at 60 V rated value 	10 A
<ul style="list-style-type: none"> • at 110 V rated value 	10 A
<ul style="list-style-type: none"> • at 230 V rated value 	10 A
Operating current at AC-15	
<ul style="list-style-type: none"> • at 24 V rated value 	4 A
<ul style="list-style-type: none"> • at 110 V rated value 	4 A
<ul style="list-style-type: none"> • at 230 V rated value 	4 A
Operating current at DC-12	
<ul style="list-style-type: none"> • at 24 V rated value 	6 A

- at 60 V rated value 5 A
- at 110 V rated value 2.5 A
- at 230 V rated value 1 A

Operating current at DC-13

- at 24 V rated value 3 A
- at 60 V rated value 1.2 A
- at 110 V rated value 0.7 A
- at 230 V rated value 0.3 A

Connections/ Terminals:

Type of electrical connection tab terminals

Ambient conditions:

Ambient temperature

- during operation -25 ... +70 °C
- during storage -40 ... +80 °C

Installation/ mounting/ dimensions:

Mounting type clip-on
Height 19 mm
Width 8 mm
Depth 31 mm

Certificates/approvals

General Product Approval

Declaration of Conformity

other



[Bestätigungen](#)

other

[Umweltbestätigung](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB24040C>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB24040C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB24040C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB24040C&lang=en

last modified:

13.02.2016