



Main

Range	Resi9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	13

Complementary

Number of ways	Incomer: 1 way N + 3 L Outgoer: 9 ways N + L
Poles configuration for 1 way	Incomer: 1 x 1P + N Outgoer: 1 x 3P + N
Connection pitch	Incomer: 18 mm Outgoer: 9 mm
Connector type	Tooth
Distance between way	Incomer: 72 mm Outgoer: 18 mm
Insulation	Insulated
Device presentation	Cuttable
Provided equipment	5 tooth cover
[Ie] rated operational current	63 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N 400 V AC Ph/Ph
[Ui] rated insulation voltage	500 V AC
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	26
Height	21 mm
Width	235 mm
Depth	24.5 mm
Colour	White (RAL 9003)
Range compatibility	Resi9 XP DM Resi9 XP ID Resi9 XP DA Resi9 XP CT Resi9 XP TL Resi9 XP SF Resi9 XP CM

Environment

Product certifications	CE
------------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins