

## DVI-28L

### Torque Multiplier DREMOPLUS ALU

2000-2800 Nm / 1500-2050 lbf-ft

Code	ETIM
2653257	EC011814
EAN	UNSPSC
4010886934449	27-11-27-20
Country of origin	eCl@ss
Germany	21-04-32-90
Customs tariff number	
82041100	



### Article description

- Especially suitable for:
  - Industry, construction sites, commercial vehicle and car workshops, agricultural technology, construction machinery
  - Bridge, ship, aircraft and railway construction, refineries
  - Machinery and plant engineering, maintenance
- Features:
  - Mechanical hand torque multiplier for controlled screw tightening and unloosening screw connections
  - With single stage planetary gearing
  - High-performance aluminium housing
  - Models with transmission ratio 1:4, 1:5.5
  - Guaranteed accuracy: Better than +/- 3 % tolerance
  - To operate with a suitable torque wrench
  - 2 models with maximum load in the range from max. 2000 Nm to 2800 Nm
  - Model -Z: with cranked reaction arm Z-shaped made of chrome vanadium steel
  - Model -L: with straight reaction arm L-shaped, with adjustable reaction square, made of light metal
  - Output square with hole for Impact sockets with locking pin and ring

### Article parts list

Torque multiplier DREMOPLUS ALU ,With offset Z-shaped reaction arm ,Adjustment table ,Detailed technical information is available on request

### Article information

Contents (Qty of pieces)	1	Output torque (max.) [lbf-ft]	2050
Net weight [kg]	2,4 kg	Total width without reaction arm	106
Total length [mm]	230 mm	Total height without reaction arm	146
Drive connector square female (metric)	20,0 mm	Backflow protection	no
Drive connector square female [inch]	3/4"	Version reaction arm	L-Form, straight
Eingangskraft [N-m]	550 Nm	Output square (metric)	25 mm
Multiplication at the ratio	1:5,5	Output square (inch)	1"
Output square	1"	Distance output square - start reaction arm (min.)	83
Input force [lbf-ft]	410 lbf-ft	Distance output square - end of reaction arm (max)	199
Output torque (max.) [N-m]	2800		