



Product data sheet

Power tools for trade & industry

Cordless Ratchet Wrench

PRO GRC 18V-60



An extremely powerful ratchet wrench that's easier to handle in narrow spaces.

The most important data

Battery voltage	18.0 V
-----------------	--------

Part Number 0 601 9N8 001

Technical data

Technical data

Weight excl. battery	0.9 kg
Battery voltage	18.0 V
Packaging dimensions (width x length x height)	365 x 440 x 155 mm
Torque, max. (hard screwdriving applications)	60 Nm
BITURBO	No

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Fast and powerful with superior ratcheting power for M5 up to M12 thanks to max output torque of 60 Nm and speed of 400 rpm
- Makes working in hard-to-reach spaces easy with compact size and long head length
- Enhanced control for different applications with mode selection for increasing or decreasing output performance levels



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

