

Han 24B-HTE2-M32/M40-w. CL



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 024 0485
Specification	Han 24B-HTE2-M32/M40-w. CL
HARTING eCatalogue	https://harting.com/19300240485

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Hood
Type	High construction

Version

Size	24 B
Version	Top entry
Number of cable entries	2
Cable entry	1x M32 1x M40
Locking type	Central locking lever (on the hood)
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Stainless steel

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	201 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140165144
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466