

**SPECIFICATION SHEET**

**Talento 371 & 372**

**PRODUCT/ORDER CODE**

Talento 371 (V86/1 DIGI 20) single channel 16 Amps

Talento 372 (V86/2 DIGI 42) two channel 2 x 16 amps

**General information**

These products are suitable for din-rail mounting.

Talento 371 is a single channel unit with 20 programme spaces.  
Talento 372 is a two channel unit with 30 programme spaces.

Features common to both products are:

Suitable for 24 hour and/or 7 day programming and control.

Built-in lithium cell giving 3 year reserve.

Automatic summer / winter changeover.

**Technical specification:**

Dimensions 85 x 35 x 60 (2-modules)

Weight 170g

AC switching capacity:

- resistive load 16A 250v AC

- inductive load  $\cos \phi 0.6$  2.5A 250v AC

- incandescent lamp load 1000W

Contact type volt-free changeover

Ambient temperature -25°C to +55°C

Accuracy typically + / - 2.5 seconds/day @ 20°C

Minimum switching time 1 minute

Manual override Advance on / off or Fix on / Fix off  
(advance on / off is self-resetting)

