

CT45 - CT HR18 Nitrile Foam Cut Glove

Collection: Portwest CT300

Range: Gloves

Materials: UHWPE

Inner Pack: 12

Outer Carton: 144

Product information

The premium CT45 cut resistant glove offers exceptional cut level D protection without the use of glass or steel fibres. Coated with Nitrile foam the CT45 offers outstanding grip in wet and dry conditions. The 100% breathable seamless liner offers outstanding comfort for the wearer.

Portwest CT300

Introducing the Portwest CT300™ collection of cut resistant gloves. State-of-the-art production techniques ensures that these gloves contain no glass or steel fibres while offering excellent levels of cut resistance. This premium collection comprises of six new styles; five gloves and one protective sleeve. Certified to the EN388:2016 standard, this collection offers outstanding cut protection levels from Level C up to the highest Level F. Under the American ANSI standard the levels range from A3 to A8. CT300™ collection is ideal for sensitive skin, offering premium hand protection for the 21st Century.

Gloves

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420 Dexterity 5

EN388:2016 +A1:2018 - (4X42D)

ANSI/ISEA 105: 2016 Type A (A4)



Features

- Level D cut resistance
- 18 gauge liner for extra dexterity
- Free from glass and steel fibres
- Nitrile foam coating for excellent grip in wet and dry conditions
- Retains cut performance level for up to 10 washes
- Breathable seamless liner
- OEKO-TEX® approved
- Retail tag which aids presentation for retail sales
- CE certified
- ANSI cut level A4
- Wash at 40°C using non-biological detergent, re-shape after wash. Do not tumble dry.

PORTWEST®

PRODUCT SPECIFICATION & TECHNICAL DATA

CT45 - CT HR18 Nitrile Foam Cut Glove

Commodity Code: 6116108000

Test House

Cert No: 2777/13848-01/E00-00

CARTON DIMENSIONS/WEIGHT

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m ³)	EAN13	DUN14
CT45G8RXS	Grey/Black	44.0	28.0	42.0	0.0400	0.0517	5036108321735	15036108810465
CT45G8RS	Grey/Black	44.0	28.0	42.0	0.0400	0.0517	5036108321711	15036108810496
CT45G8RM	Grey/Black	44.0	28.0	42.0	0.0600	0.0517	5036108321704	15036108810489
CT45G8RL	Grey/Black	44.0	28.0	42.0	0.0600	0.0517	5036108321698	15036108810472
CT45G8RXL	Grey/Black	44.0	28.0	42.0	0.0600	0.0517	5036108321728	15036108810502
CT45G8RXXL	Grey/Black	44.0	28.0	42.0	0.0600	0.0517	5036108321742	15036108810519