

Features

- Accepts cable diameters of upto 8mm
- Can be used with a maximum panel thickness of upto 16mm Thick.
- REACH and ROHS Compliant

RS PRO Black Polychloroprene 11.5mm Sleeved Cable Grommet for Maximum of 8mm Cable Dia

RS Stock No.: 0428020



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This 11.5 mm round sleeve cable grommet from RS PRO is designed for easy installation, providing protection for wires while ensuring a neat and organised setup. To use, simply cut a hole to the required size, insert the grommet into the panel, and pass the cable through the sleeve opening.

It accommodates cables with diameters between 1 mm and 8 mm, the sleeve offers additional security protection for your wiring. This sleeve grommet is compatible with panels up to a maximum thickness of 16 mm.

Made from black polychloroprene rubber, it is suitable for temperatures ranging from -30°C to +90°C.

Specifications

Grommet Type	Sleeved / Flange Cable Grommet
Material	Polychloroprene
Colour	Black
Maximum Panel Thickness	16mm
Minimum Cable Diameter	1mm
Maximum Cable Diameter	8mm
Panel Hole Diameter	11.5mm
Minimum Operating Temperature	90°
Maximum Operating Temperature	-30°

Approvals

Standards Met	REACH, RoHS
---------------	-------------