

29584

Aluminium Handle, Ø25 mm,
1260 mm, Red



This handle with colour-coded grip can be used with any product in the Vikan range.

Technical Data

Item Number	29584
Material	Anodised Aluminium Polypropylene
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	900 Pcs.
Quantity Per Layer (Pallet)	50 Pcs.
Box Length	1270 mm
Box Width	150 mm
Box Height	70 mm
Product Diameter	25 mm
Length/Depth	1260 mm
Width	25 mm
Height	25 mm
Gross Weight	0,32 kg
Net Weight	0,3 kg
Cubik metre	0,0008 M3
Recommended sterilisation temperature (Autoclave)	100 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature ³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	8 pH
Recycling Symbol "7", Miscellaneous Plastics	No
GTIN-13 Number	5705020295843
GTIN-14 Number (Box quantity)	15705020295840
Commodity Code	76082020
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.