

# Indicator

17-  
371351Z

Distribution by  
Rs-online



<https://rs-online.eao.com/p/17-371351Z>

Your product:

---



## 17-371351Z Indicator

### FRONT

|                  |                |
|------------------|----------------|
| Front dimension: | Ø 18,3 mm      |
| Front form:      | Round          |
| Reflector:       | Plastic, Black |

### MOUNTING

|                   |                |
|-------------------|----------------|
| Design:           | Raised         |
| Mounting cut-out: | Ø 16.2 mm      |
| Mounting type:    | Panel mounting |

### OPERATING-/INDICATION PART

|                      |       |
|----------------------|-------|
| Lens:                | round |
| Illumination colour: | Green |

### ELECTRICAL CHARACTERISTICS

|                    |                                                                                 |
|--------------------|---------------------------------------------------------------------------------|
| Operating voltage: | 24 V DC $\pm 10\%$                                                              |
| Operation current: | 15 mA $\pm 15\%$                                                                |
| Lumi. Intensity:   | 980 mcd                                                                         |
| Polarity:          | Anode (+) Brass plug-in connector<br>Cathode (-) Brass tinned plug-in connector |

### MECHANICAL CHARACTERISTIC

|                    |                                |
|--------------------|--------------------------------|
| Terminal:          | Plug-in terminal, 2.8 x 0.8 mm |
| Tightening torque: | Fixing nut max. 0.2 Nm         |

**Weight:** 0.007 kg

## AMBIENT CONDITION

**IP Protection:** IP40 front side, IP65 front side, according to IEC 60529

**Operating temperature:** – 20 °C ... + 60 °C

**Storage temperature:** – 25 °C ... + 80 °C

## CERTIFICATE

**Approbations:** UL

**Conformities:** 2011 / 65 / EC (RoHS), 2014 / 35 / EU (230 VAC)

**REACH:** REACH compliant

**RoHS:** RoHS compliant


## OTHER

**Short Description:** Indicator, Ø 16.2 mm, Ø 18,3 mm, Round, Plug-in terminal, 2.8 x 0.8 mm, Green


**Kind of illumination:** Single-LED

**Hints:** Connectors: Brass terminal = anode (+); brass tinned terminal = cathode (-), IP67 front side gap between LED and reflector and gap between reflector and frontplate sealed to IP67 when using the supplied gasket., The plastic is limited resistant to chemicals.


**Wiring diagrams:**



**Mounting cut-outs:**



**Dimension drawings:**



A = Protection tube (only 230 VAC)

B = 1 gasket

C = flat

conical

D = round