

# VARTA Recharge Accu Power AA 2100 mAh OEM



The most powerful product line with durable and precise energy supply for all standard and smart applications of daily use.



## Information

- Pre-charged and with 'ready to use' technology - for immediate usage straight from the pack
- Rechargeable hundreds of times without memory effect
- Suitable for all standard and smart devices of daily use and all NiMH chargers
- Best use in high drain applications and devices with constant energy requirements like LED flashlights, GPS systems, wireless mice and more
- Lasts up to 8 times longer in digital cameras\*
- \* vs. VARTA Energy. Based on IEC 60086-2 (ed. 14.0) HDA-Test (high drain application). May vary by device.

## Article Details

Ordernumber	56706 101 111
Customs Tariff Number	85075000
Country Of Origin	China
IEC	HR6
Others	56706, AA, Stilo
Nominal Capacity	2100 mAh
Voltage	1.20
System	Nickel Hydride
Consumer Unit	1
DG Profile	NiMH battery UN3496 (sea to 100kg ok)

## Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 550906				0.03
SK2 (Inner carton 2)						
SK1 (Inner carton 1)	10	40 08496 550913	144.00	16.00	51.50	0.31
VSK (Master carton)	200	40 08496 591459	155.00	215.00	93.00	6.24
PAL (Pallet)	33600	40 08496 591466	800.00	1,200.00	801.00	1,068.48
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
7	24		168		10	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany  
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

