



Lighting **excellence**



@4liteuk



@4liteuk



@4lite



@4liteuk

Lorica

Lorica Rectangular Photocell Bulkhead

Code: 4L2/3212/PC

Application Commercial, Industrial

Product Features

- Unique Visiluxe diffuser allows 90% light transmission from LED source for increased performance
- CCT selectable between 3000K and 4000K
- Non-dimmable
- Unique Visiluxe diffuser allows 90% light transmission from LED source for increased performance
- Instant light output and unlimited switching

Technical Information

Wattage	6W - 9W
Lumens Delivered	570lm - 960lm (4000K)
Lm/W	114lm/W - 119lm/W (4000K)
Beam Angle	120
CRI	80
CCT	3000/4000K
Input	220-240V
Operating Temp	-10°C - 40°C
SDCM	6
Product Weight without Packaging	0.46 kg

Technical Information

Light Source	LED
Colour / Finish	Black
IP Rating	IP65
Class Protection	2
Internal / External	Internal / External
Mounting Option	Ceiling, Wall
Lumen Depreciation	L70 >54,000h
Warranty (Years)	5
CE Mark	Yes
Diameter	0 mm
Height	76 mm