

# HyFlex<sup>®</sup> 11-600/605

## General Purpose

Orig	17-02-2004
Rev	14-07-2010

### Product description

Supported polyurethane protective gloves.

### Glove material

- Polyurethane coating
- Nylon liner ( ref. 11-600 & 605 )
- Natural rubber in the elastic

### Possible Harmful ingredients

Sensitizers:

- Natural rubber proteins

Only a very small number of users may be sensitised to any of these ingredients and hence may develop irritant and/or allergic reactions.

No Substances of Very High Concern ( as per REACH Regulation 1907/2006 )

### Properties

- Superior comfort; no seams on the inside of the gloves
- Superior flexibility and finger dexterity
- Machine washable at 40°C

### EN test data

Abrasion resistance :

11-600:Performance level 3 (2000-8000 cycles)

11-605 : Performance level 0 ( < 100 cycles )

Blade cut resistance :

11-600 : Performance level 1 ( index 1.55 )

11-605 : Performance level 0 ( index 1.1 )

Tear resistance : Performance level 3 ( min. 50 N )

Puncture resistance :

11-600: Performance level 1 (min. 20 N)

11-605: Performance level X (not applicable)

### European conformity

Gloves conform to the requirements of the European Directive 89/686/EEC and to the European standards EN 420:2003 and EN 388:2003. They are categorised in "Intermediate Design" (= Protection against intermediate risks).

EC-type examination certificate received from:

**CENTEXBEL**

*Technologiepark 7*

*B-9052 Zwijnaarde*

### Application- Limitations of use

Hand protection - light duty applications.

For detailed information, please contact Ansell.

Do not use against flames or temperatures

< - 25°C or > 100°C.

Do not use against chemicals; the gloves are not liquidproof.

Do not use for heavy duty mechanical applications.

### Storage

Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.

Type	Style	Colour	Reference	(EN) Sizes	Length
Palm coated	Knitwrist	white	11-600	6, 7, 8, 9, 10, 11	210 – 260 mm
Fingertip coated			11-605	6, 7, 8, 9, 10	195 – 235 mm

The length of the gloves are below the EN requirements for total minimum glove length. Hence, the glove is called 'Fit for special purpose'.

### **Ansell Healthcare Europe N.V. (European Head Office)**

Riverside Business Park, Spey House Boulevard International 55 B-1070 Brussels, Belgium  
Tel. +32 (0) 2 528 74 00 Fax +32 (0) 2 528 74 01 Fax Customer Service +32 (0) 2 528 74 03

### **Ansell (UK) Limited**

30-32 Mariner Lichfield Road Industrial Estate Tamworth Staffordshire B797UL, United Kingdom  
Tel. +44 1827 302100 Fax +44 1827 302101  
http://www.anselleurope.com E-mail info@eu.ansell.com



ISO 9001 Certificate  
Number FM 40130