

PREVOS1 SAFETY QUICK COUPLINGS - ESI 07

Female threaded swivel coupler

Profile : EUROPEAN



Part number	Female thread	Min. operating pressure (bar)	Flow rate at 6.00 bar (l/min) ($\Delta P = 0.60$ bar)	ID passage (mm)	Temperature min/max (°C)
ESI 071101SW	G1/4	2.00 / 12.00	1820.00	7.4 mm	-15.00 / 70.00

Part number	Dim. A (mm)	Dim. B (mm)	Dim. C (mm)
ESI 071101SW	176.30	32.25	128.60

