

Endress+Hauser FTL325P-H1A1

Nivotester FTL325P



Level instrument, point level. Input: 1/3-channel, 2-wire PFM.

Picture for reference only. Product appearance may vary based on configuration

Configuration of FTL325P-H1A1:

Approval:	H	ATEX II (1)GD [Ex ia] IIC,WHG, SIL,IECEX [Ex ia] IIC
Housing:	1	Rail mounting, 22.5mm, 1-channel
Power Supply:	A	85-253VAC
Switch Output:	1	1x SPDT level + 1x SPST alarm

Alternative part number: FTL325P-H1A1