

Features

- Snap fit latch for securing panels
- Plunger and grommet supplied as a set
- Grommet retains in removable panel
- Releasable
- Installed by hand
- Ideal for applications that require regular maintainance

RS PRO Rivets

RS Stock No.: See Table



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Designed to offer a quick, easy joining and securing of panels
- Ideal for applications that require regular maintenance work
- Push the grommet into the removable panel, insert the plunger, then insert the assembly into the fixed panel
- Suitable for electrical equipment, enclosures, telecoms, appliances etc

Material Specifications

Materials	Grommet: Polycarbonate Plunger: Nylon 6
Rivet Type	Rivet Set
Colour	Black
Finish	Plain
Flammability Rating	UL94-V2
Working Temperature Range	-40°C to +85°C

Part Specifications

Parameters	0304167	0304165
Top Panel Hole Diameter	7.5mm – 7.7mm	7.5mm – 7.7mm
Top Panel Maximum Thickness	1.6mm	1.6mm
Bottom Panel Hole Diameter	8.0mm – 8.2mm	8.0mm – 8.2mm
Total Panel Thickness / Grip Range	2.0mm – 4.2mm	2.0mm – 4.2mm
Plunger Head Diameter	16.0mm	9.4mm
Plunger Head Height	9.5mm	6.5mm
Figure	1 (SLPL)	2 (SLPB)

