

CD-HF 25X25 - Cable duct



3240340

<https://www.phoenixcontact.com/gb/products/3240340>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, light gray, halogen-free, comprising upper part and mounting base, width: 25 mm, height: 25 mm, length: 2000 mm

Your advantages

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool
- Fast and seamless creation of T and cross connections by means of an additional predetermined breaking point in the cable duct base

Commercial data

Item number	3240340
Packing unit	24 pc
Minimum order quantity	24 pc
Sales key	BE7441
Product key	BE7441
Catalog page	Page 579 (C-3-2019)
GTIN	4046356507257
Weight per piece (including packing)	388 g
Weight per piece (excluding packing)	480 g
Customs tariff number	39259020
Country of origin	DE

CD-HF 25X25 - Cable duct

3240340

<https://www.phoenixcontact.com/gb/products/3240340>



Technical data

Product properties

Product type	Wiring duct
--------------	-------------

Dimensions

Width	25 mm
Height	25 mm
Length	2000 mm

Material specifications

Color	light gray (RAL 7035)
Material	PC/ABS
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1, HL 2, HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1, HL 2, HL 3
Components	halogen-free

Cable/line

Halogen-free	yes
--------------	-----

Mechanical properties

Usage cross-section	327 mm ² (100 %)
Number of cables at 60% filling volume	10 (2.5 mm ² Ø 3.4 mm)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

CD-HF 25X25 - Cable duct

3240340

<https://www.phoenixcontact.com/gb/products/3240340>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240340>



CSA

Approval ID: 80202282



VDE approval of drawings

Approval ID: 40058453

DNV

Approval ID: TAE00004VN



UL Recognized

Approval ID: E328576

CD-HF 25X25 - Cable duct

3240340

<https://www.phoenixcontact.com/gb/products/3240340>



Classifications

ECLASS

ECLASS-13.0	27400703
-------------	----------

ETIM

ETIM 9.0	EC000012
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD-HF 25X25 - Cable duct

3240340

<https://www.phoenixcontact.com/gb/products/3240340>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk