

1696

spirit levels made from anodized profile aluminium, with 2 unbreakable vials, accuracy: 1 mm/m

- Precision 1 mm/m
- Adjustable horizontal vial

	art.	L mm	H mm	S mm	g	
016960002	1696 200	200	50	19	136	
016960004	1696 400	400	50	19	259	
016960005	1696 500	500	50	19	325	
016960006	1696 600	600	50	19	376	
016960008	1696 800	800	50	19	498	
016960010	1696 1000	1000	50	19	589	

