

Comfortable nitrile cleanroom gloves, compatible with Class 100 (ISO 5) cleanroom environments

- **Improved protection and durability:** TouchNTuff® 93-300 nitrile cleanroom gloves are comfortable and robust, ensuring strong chemical splash resistance and resistance against punctures and tears
- **Safeguarded product integrity:** These nitrile gloves are entirely silicone-free, preventing potential contaminant transfer and safeguarding product integrity
- **Assured cleanliness:** They are also designed to be compatible with Class 100 (ISO 5) cleanroom environments, delivering hand protection that is reliable and fit for purpose



KEY FEATURES & BENEFITS

- **Robust nitrile formulation:** Puncture, tear and chemical splash resistance
- **Silicone-free design:** Improved product protection
- **Class 100 (ISO 5) cleanroom compatibility:** Assured cleanliness

Industries

- Biotechnology Manufacturing
- Electronics manufacturing

Recommended For

- Clean room cleaning and preparing
- Blending, compounding solids and liquids
- Spill or leakage cleanup
- Transferring liquids and solids
- Loading centrifuges and chromatography columns
- Assembly of parts
- Weighing and dispensing of solid and liquid raw materials

TECHNICAL DATA SHEET

	Product Information
Material	Nitrile
Color	Green
Shape	Ambidextrous
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 13485, ISO 14001, ISO 9001
Regulatory/Standard Compliance	ASTM D6319, CE 0493, Category III, EN 455 Part 2, EN ISO 21420:2020, EN ISO 374-1:2016, EN ISO 374-5:2016, EN 421:2010, FDA21 CFR 177-2600-US Food Contact Approved, UKCA
Packaging	50 gloves per vacuum sealed polybag; 2 polybags per master polybag; 10 master poly bags per poly lined case More sustainable packaging: These nitrile gloves are packed in recyclable plastic packaging* and delivered in recycled cardboard shipper cases. *Inner wrap, pouch, bag and liner are made from polyethylene (PE) based film. Always check your local recyclable status as these materials may not be considered suitable for recycling in your location.
Storage	Keep away from direct sunlight; store in a dry place and keep in the original packaging. Keep away from ozone sources. If products are properly stored, as indicated, they won't lose their performances or change characteristics significantly. If products could be affected by ageing or storage, the expiry date is mentioned on the packaging materials.
Country of Origin	Thailand
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Powder Content	Powder-Free
External Glove Surface	Textured Fingers
Internal Glove Surface	Powder-Free, Chlorinated
Cleanroom Class	Class 100/ISO 5
Shelf Life	3 Years
Tested for use with Chemotherapy Drugs	Yes
Protein Level	N/A: contains no natural rubber latex
Anti-static	Yes
Vulcanization Chemical Accelerators	Zinc Dibutyldithiocarbamate (ZDBC) <i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i>

Physical Properties		Testing Method
Typical Length (mm/in)	300 / 12	EN ISO 21420
Freedom from Holes	1.5 AQL	EN 374-2
Typical Particle Count $\geq 0.5\mu\text{m}$ (counts / cm^2)	$\leq 1,200$ particles / cm^2	IENT-RP-CC005.4
Target Single Wall Palm Thickness (mm/mil)	0.13 / 5.1	EN 455-2
Target Single Wall Finger Thickness (mm/mil)	0.16 / 6.3	EN 455-2
Target Single Wall Cuff Thickness (mm/mil)	0.08 / 3.1	EN 455-2
Ultimate tensile strength (MPa) During Aging	≥ 14	ASTM D412-06a
Force at Break (N) During Aging	≥ 9	EN 455-2

ORDERING INFORMATION

SIZE	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
REORDER NO.	93300060	93300070	93300080	93300090	93300100

PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.