



182.72.104.66PASEStehlager-Gehäuseeinheiten

## Plummer block housing units

### PASE20-XL-N (Series PASE)

cast iron housing, radial insert ball bearing with eccentric  
locking collar, P seals

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

d	20 mm
L	130 mm
H <sub>2</sub>	64 mm
A	32 mm
A <sub>1</sub>	19 mm
B <sub>1</sub>	31 mm
d <sub>3</sub> max	33 mm
H	33,3 mm
H <sub>1</sub>	14,5 mm
J	97 mm
N	11 mm
N <sub>1</sub>	19 mm
Q	Rp1/8
S <sub>1</sub>	23,5 mm
m	0,6 kg Mass
C <sub>r</sub>	13600 N Basic dynamic load rating, radial
C <sub>0r</sub>	6600 N Basic static load rating, radial
	ASE04 Designation of housing
	GRAE20-XL-NPP-B Designation of bearing
	KASK04 Bearing end cap, closed design. To be ordered separately.
	Slot for bearing end cap

