

WINSTA® MINI

Intermediate Coupler and Distribution Connectors, 3-Pole

1
23

1

250 V/4 kV/3 I_N 16 A	250 V/4 kV/3 I_N 16 A	250 V/4 kV/3 I_N 16 A
② Approvals	② Approvals	② Approvals





Color	Item No.	Pack. Unit	Color	Item No.	Pack. Unit	Color	Item No.	Pack. Unit
Intermediate coupler , 1 x plug/1 x socket			h-distribution connector, unidirectional, plug/socket – socket			T-distribution connector, 1 x plug/2 x socket		
● black	890-603	50	● black	890-634	50	● black	890-606	25
○ white	890-653	50	○ white	890-684	50	○ white	890-656	25
At least one snap-in connector WITHOUT locking lever is required on one side when connecting two lights directly via intermediate coupler (see page 22).			for "flying leads", with 3rd locking lever			for "flying leads", with 3rd locking lever		
● black	890-636	50	● black	890-636	50	● black	890-615	25
○ white	890-686	50	○ white	890-686	50	○ white	890-665	25

Item-Specific Accessories

Mounting plate, for distribution connectors			Fixing pin, for mounting plates		
					
● black	890-623	100	③ black	890-601	250
○ white	890-673	100			

Accessories, 890 Series

Locking lever, for "flying leads", manually operated			Locking lever, for "flying leads", tool operated		
					
● black	890-101	100 (2x50)	● black	890-111	100 (2x50)
○ white	890-121	100 (2x50)	○ white	890-131	100 (2x50)

Dimensions

