

# 0 601 9H2 170 – Bosch GO

Material number	0 601 9H2 170
EAN	4059952548746
1 x screwdriver bit PH2 2 608 521 M11	✓
25-piece screwdriver bit set	✓
L-BOXX Mini 1 605 438 1GK	✓
Micro USB cable 1 607 000 CG9	✓
USB adapter 2 609 120 718	✓



## Technical data

### Technical data

Torque (soft/hard/max.)	2.5/5/- Nm
No-load speed (1st gear / 2nd gear)	– 360 rpm
Battery type	Lithium-ion
Chuck capacity, min./max.	6.35 mm
Weight excl. battery	0.31 kg
Packaging dimensions (width x length x height)	162 x 280 x 90 mm
Drill chuck, version	1/4" with internal hexagon shank
Battery capacity	1,5 Ah
Battery voltage	3.6 V
Weight incl. battery	0,3 kg
Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level dB(A); Sound power level dB (A). Uncertainty K= dB.



### Screw diameter

Max. screw diameter	5 mm
---------------------	------

### Noise/vibration information

Sound pressure level	70 dB(A)
Sound power level	80 dB(A)
Uncertainty K	3 dB

## Sales information

---

### Positioning

- The Bosch GO Cordless Screwdriver – Minimum Effort, Maximum Efficiency

### User benefit

- Dual-activation mode – simply push machine forward or press 'on' button to begin
- Mechanical clutch – select from 5 torque settings up to 'maximum performance mode'
- Easy-to-control – tool stops immediately after deactivation via an electronic brake