

Hot air tool

HM 2020 E

Case set

EAN 4007841 089566

Article number 089566



series 3

2200 W

2200 W Output

Display

Display (LCD)



80 – 630°C



stepless adjustable



150 – 500 l/Min.



3 air volume levels



Suitable for
pluggable nozzles



VDE



CE

Function description

The HeatMatic 2020 E is electronically controlled and perfect for ambitious projects. With 2200 W, it can be regulated from 80 to 630°C via the display.

Technical specifications

Temperature	80 – 630 °C
Airflow rate	150 – 500 l/min
Temperature setting	in 10°C steps by joystick
Settings made via	joystick
Temperature display	LCD display
Airflow control	Settings
Programming function	No
Residual heat indicator	Yes
Motor, type	Brush motor
Heating element	Ceramic heating element
Mains power supply	220 – 230 V / 50 – 60 Hz
Function, hanger	Yes
Restart protection	No

Temperature scanner	Yes
Fine dust filter	No
Thermal cut-out	Yes
Thermostat	Yes
Cord length	2.2 m
Dimensions (L x W x H)	253 x 86 x 200 mm
PU1, net weight	0,88 kg
Manufacturer's Warranty	3 years
PU1, EAN	4007841089566
Scope of delivery	incl. reducing nozzle
Output	2200 W
Product category	Hot air tool

Accessories

EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 009571	Reduction nozzle
EAN 4007841 070618	Reduction nozzle

<https://www.steinel.de>

Subject to technical modifications

03.2025 Page 1 from 2

Hot air tool

HM 2020 E

Case set

EAN 4007841 089566

Article number 089566



Accessories

EAN 4007841 070717	Reduction nozzle
EAN 4007841 074616	Soldering reflector nozzle 10 mm
EAN 4007841 053963	Hot Air Tool Guard Cage HL 1820 S - HG 2320 E
EAN 4007841 014919	Temperature scanner HL Scan
EAN 4007841 070311	Window nozzle
EAN 4007841 070410	Window nozzle
EAN 4007841 070113	Surface nozzle
EAN 4007841 070212	Surface nozzle
EAN 4007841 070519	Reflector nozzle
EAN 4007841 087715	Flat angled nozzle 40x2 mm for discharge pipe bead
EAN 4007841 068035	Adapter nozzle
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E
EAN 4007841 075569	12-piece hot-air accessory kit