

## FEATURES

- Low voltage power lamp for cost saving energy efficiency
- LEDs are long lasting and produce no heat
- Re-enforced tempered glass lens provides impact resistance
- Robust build for a long service

# RS PRO LED Machine Light, 100 → 260 V ac, 12 W, Adjustable Arm, 215mm Reach, 430mm Arm Length

RS Stock No.: 777-7987



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From our high quality RS Pro brand, this LED task light is perfect addition to your workstation. With six efficient LED bulbs, the machine light has a bright, white output, so you can enjoy shadow-free lighting for clear and comfortable working.

The LED light features an adjustable arm, with a single point of articulation to ensure you have the light you need where you need it. There is even a built in handle on the light head for further ease of adjustment.

## General Specifications

<b>Lamp Type</b>	LED
<b>Light Style</b>	Articulated Arm
<b>Lamp Supplied</b>	Yes
<b>Integral transformer</b>	Yes
<b>Shield Fitted</b>	No
<b>Switch Fitted</b>	No
<b>service life</b>	up to 40,000hours
<b>Arm Type</b>	Adjustable

## Electrical Specifications

<b>Mains Plug Type</b>	Type C – Euro plug
<b>Voltage Rating</b>	100VAC to 260VAC
<b>Wattage</b>	12W
<b>EU Energy Efficiency Rating</b>	A+
<b>Number of Bulbs</b>	6
<b>Colour Temperature</b>	5700K

## Mechanical Specifications

<b>Arm Length</b>	430mm
<b>Cable Length</b>	1.8m
<b>Maximum Reach</b>	215mm
<b>Beam Angle</b>	60°

## Operation Environment Specifications

Temperature Range	-30°C to 60°C
-------------------	---------------

## Protection Category

IP Rating	IP 65
-----------	-------

## Approvals

Compliance/Certifications	RoHS Certificate of Compliance , CE Approved
---------------------------	--





