

Product specifications **380BV**

Last update: 3/12/08 4:16:21 PM

**General**

Description	<b>Dunlop Pricemastor</b>
Upper/Sole Color	<b>White/Green</b>
Status	<b>Stock,</b>
Segment	<b>N/A</b>
Product line	<b>Volume</b>
Sizerange/#	<b>35-47/13</b>
Hangtag	
Insole	
Lining	<b>Nylon flat</b>
Resistance code	<b>4</b>



380BV

**Safety**

Standard	<b>CE</b>
	<input type="checkbox"/> <b>Steel Toecap</b> <input type="checkbox"/> <b>Antistatic</b>
	<input type="checkbox"/> <b>Steel Midsole</b> <input type="checkbox"/> <b>Energy absorbing</b>
	<input type="checkbox"/> <b>Oilresistant sole</b> <input type="checkbox"/> <b>Cold insulating</b>
Safety marking	
Manual	<b>Printed on polybag</b>

**Sole info**

Sizing	<input checked="" type="checkbox"/> <b>French</b> <input checked="" type="checkbox"/> <b>Enlish</b> <input type="checkbox"/> <b>U.S.A.</b>
Date of manufacturing	<input checked="" type="checkbox"/>
Other sole info	<b>CE Plan.Plast. Made in P. Pict. R.boot</b>

**Labeling/marketing**

Marking	<b>Dunlop stamp</b>
Barcode on boot	<b>Barcode label</b>
Barcode packaging	<b>Dunlop label</b>
Barcode outercarton	<b>Dunlop label</b>

**Remark**

Compounds: PC930white1100 PR022green1629 Weight 42: 2,10 kg/pr

<b>Packaging</b>		<b>Sealed milky polybag</b>						
Size	Boxtype	Length	Width	Height	Pairs/Box	Boxes/layer	#Layers	Pallet height
<b>35-37</b>	<b>PT2</b>	<b>390</b>	<b>390</b>	<b>360</b>	<b>8</b>	<b>6</b>	<b>5</b>	<b>1.95</b>
<b>47</b>	<b>PT5</b>	<b>390</b>	<b>390</b>	<b>585</b>	<b>8</b>	<b>6</b>	<b>3</b>	<b>1.92</b>
<b>38-43</b>	<b>PT3</b>	<b>390</b>	<b>390</b>	<b>395</b>	<b>8</b>	<b>6</b>	<b>4</b>	<b>1.75</b>
<b>44-46</b>	<b>PT4</b>	<b>390</b>	<b>390</b>	<b>430</b>	<b>8</b>	<b>6</b>	<b>4</b>	<b>1.8</b>