


Abisolierlänge: 13mm
stripping length: 13mm
 Anzugsmoment: 16mm² 25mm² 35mm²
Tightning torque: 6Nm 7Nm 8Nm
 für Litze 16-35mm², AWG 4-2, feindrähtig
for stranded wire 16-35mm², AWG 4-2, fine wire



All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maß/Free size tolerances		
				Dat.	Name	Maßstab/Scale 2:1	100A Axialschraubkontakt, Stift 100A axial screw contact, male 16-35mm ² versilbert/silver plated	
			Detail.	15.07.11	gru			
			Insp.		Rü			
			Stand.					
A			HARTING Electric GmbH & Co. KG				TB 09 11 000 6113	
Mod.	Dat.	Name	D-32339 Espelkamp					
						Sub.	Blatt/page	