

Technical data sheet

Article number:
111-12821

T120S



Product Group	Cable Ties for temperatures up to + 105°C (heat stabilised)
Product Family	T-Series in PA66HS black
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, EVOcut, MK9P, MK9P w/ Upper air, MK10-SB, MK21, EVO9, EVO9SP, EVO9HT, EVO9i, EVO9iSP, EVO9iHT
Bundle Ø max.	55.0 mm
Bundle Ø min.	5.0 mm
Flammability	UL 94 V2
Halogen-free	Yes
Height (H)	7.7 mm
Length (L)	225.0 mm
Min.Tensile Strength	535 N
Operating Temperature	-40 °C to +125 °C
Package Content packed in	pack
Pack Cont.	500 pcs.
Releasable Closure (Yes/No)	No
Specifications	UL 62275
Thickness (T)	1.6 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E64139
UV-resistant acc. to ASTM D6779 (Yes/No)	No
Variant	Inside Serrated
Weight/Unit	0.003219 kg
Width (W)	7.6 mm

