



1300 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Peli™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Peli cases have survived.

Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Watertight, crushproof, and dustproof**
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Easy open double-throw latches
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Pick N Pluck™ with convoluted lid foam
- Peli's legendary lifetime guarantee**
- * Where applicable by law



CONFIGURATIONS



1300
Standard



1300NF
No Foam



1300WF
With Foam

DIMENSIONS

Interior (L×W×D)	9.17 x 7.00" x 6.12 (23.3 x 17.8 x 15.5 cm)
Exterior (L×W×D)	10.62 x 9.68" x 6.87 (27 x 24.6 x 17.4 cm)
Lid Depth	1.18" (3 cm)
Bottom Depth	4.93" (12.5 cm)
Total Depth	6.11" (15.5 cm)
Int Volume	0.23 ft ³ (0.007 m ³)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Orange	 Silver	 Yellow
---	--	--	--

WEIGHT

Weight With Foam	3.53 lbs (1.6 kg)
Weight Empty	3.09 lbs (1.4 kg)
Buoyancy	12.35 lbs (5.6 kg)
Master Pack Weight	16.85 lbs (7.64 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	190°F (87.8 °C)

CERTIFICATIONS

IP67	
Def Stan 81-41	

OTHER

Master Pack	4
Military	yes

ACCESSORIES

				
1203 Replacement O-ring	1301 4 pc. Replacement Foam Set	1200PF Special Application Panel Frame	1507QM Quick Mounts - set of 4	1506TSA TSA Lock
				
1500D Desiccant Silica Gel				