

590 - 592

direct reading torque wrenches for right-hand and left-hand tightening torque
accuracy: $\pm 4\%$

UNI EN ISO 6789

Nm
 Kgfm
 lbf.in
 ■
 A
 mm
 L
 mm
 ■
 kg



	art.	Nm	Kgfm	lbf.in	■	A mm	L mm	■ kg	■
005900001	590	0,8÷4	0,08÷0,4	7÷35	1/4	60	253	0,52	0,1
005900003	590/1	2,5÷12,5	0,25÷1,25	21÷110	1/4	60	253	0,52	0,5
005920005	592/3	1÷27	0,1÷2,7	10÷240	3/8	70	253	0,52	1,0
005920007	592/4	8÷40	0,3÷4	20÷360	3/8	70	253	0,52	1,0