ANSMANN USB POWER

POWERBANKS USB CHARGERS CHARGE CABLES



WHAT EXACTLY IS

POWER DELIVERY?

Power Delivery is a new quick-charging standard which can deliver up to 100 Watts by means of the new USB Type-C connector. This means that not only small devices, such as smartphones, can be charged via USB Type-C, but that compatible notebooks, for example the Apple MacBook Pro, now no longer require an extra mains adapter.

Please note that the device to be charged and the cable must be Power Delivery compatible.

MAXIMUM POWER!

Power Delivery can **output up to 100 Watts**. This places it far ahead of the competition. Amongst other things, it also enables notebooks to be charged via USB Type-C.









USB STANDARD



IMPOSSIBLY FAST!

Power Delivery charges compatible device **up to 20 times faster** than the USB standard. Here is a comparison of the charge speed for an iPhone XS Max.











USB STANDARD

3 hours, 15 minutes

COMPATIBLE WITH ALL!

With 1-100 Watts, Power Delivery is **compatible with almost any device that can be charged via USB**. Wireless charging can also be speeded up with Power Delivery.







Tablets 5-18 Watts



Mobile consoles 10-30 Watts



les Notebooks s 30-100 Watts













Power Deliver











EXTREMELY HIGH DEGREE

In combination with our devices, Power Delivery offers 5 protective functions.



Overheating protection



OF SAFETY!

Overload protection (current + voltage)




Deep discharge protection



Short-circuit protection




Automatic shutdown




THE NEW ANSMANN POWERBANKS

WHICH IS THE ONE FOR YOU?

With the ANSMANN Powerbank you can find the perfect, up-to-date match. There is a choice of 10 models to cover every need. In order to help customers to find "their" Powerbank quickly and easily, the functions and characteristics are presented informatively and intuitively. The icons and graphics are repeated on the packaging, helping customers to navigate to the most suitable product!





STANDARD FEATURES IN ALL POWERBANKS



ANSMANN QUALITY

High-quality powerbanks made of aluminium or hard plastic.
Connections made from aluminium.



UNIVERSAL USE

Common standard connections enable smartphones, tablets etc. to be charged.



GUARANTEE

You are always safe with us. If you have questions or problems with the product, you can rely on our manufacturer's guarantee!



MULTISAFE TECHNOLOGY

The safety technology protects you and your device. Over-charging protection, deep discharge protection, short-circuit protection, automatic shut-down

SPECIAL FEATURES



Fast charging technologies Enable **ultra fast charging** of compatible tablets and smartphones



Lighter and smaller **extra compact** Powerbank, perfect to put in a pocket



Has at least one **USB A** and one **Type-C output**



Future-proof: With the new and flexible USB
Type-C connection



Your device can be wirelessly charged with this Powerbank



Can be charged via
Micro-USB or USB Type-C





Freely available guick-charge function.



Certified quick-charge function from Qualcomm.

OUR NEW

POWER PACK

POWERBANK 8 WIRELESS

POWER DELIVERY + USB TYPE-C QUICK-CHARGE COMPATIBLE

Wireless charging for convenient charging

















FAST, FASTER, FASTEST

POWERBANKS WITH POWER DELIVERY





POWERBANK 10.000

POWER DELIVERY + QUICK CHARGE 3.0

USB Type-C PD and USB QC3.0 10.000 mAh | 2x input, 3x output Ultra-fast charging with Power Delivery

Part No. 1700-0148













POWERBANK 20.000

POWER DELIVERY + QUICK CHARGE 3.0

USB Type-C and USB QC3.0 20.000 mAh | 2x input, 3x output Ultra-fast charging with Power Delivery











LESS IS MORE

SMALL IN SIZE, BIG ON POWER





POWERBANK 10.8 MINI

Ultra compact 10.000 mAh | 1x input, 2x output Hardly bigger than a bank card Part No. 1700-0091







TIME TO KEEP IT SIMPLE

POWERBANKS WITHOUT THE BELLS AND WHISTLES



POWERBANK 30

Pure power in a smart design 30.000 mAh | 3x input, 2x output For everything you need on the go Part No. 1700-0134



POWERBANK 20

The all-rounder 20.000 mAh | 2x input, 2x output Universal and flexible Part No. 1700-0133



POWERBANK 10

Super slim - fits in a pocket 10.000 mAh | 2x input, 2x output Small but nice, ideal for on the go


























CONNECTIONS FOR EVERY SITUATION

ANSMANN USB CHARGERS

Whether USB, USB Type-C, whether one, two or even five devices. With the modern and contemporary ANSMANN USB chargers, you can charge almost any device.

CHARGE POWER













SPECIAL FEATURES





This charger can be used for wireless



ULTRA-FAST CHARGING

You can charge your device at ultra-fast speed thanks to the quick-charge technology in our **USB** chargers



Future-proof: With the new and flexible USB Type-C connection



LIGHT AND COMPACT

The small, light and extra compact USB charger,



Applies to all devices: Automatically charges with the fastest possible charging speed



POWER DELIVERY

New, freely available USB Type-C fast charging standard.



POWER DELIVERY WITH PPS

Intelligent charging control charges devices even more efficiently.




QUALCOMM QUICK CHARGE 3.0

Certified quick-charge function from Qualcomm.









WIRELESS CHARGER WILINE 15R

WIRELESS QUICK CHARGING FUNCTION

Our extra-slim induction charger with a maximum 15 Watt power! 15 Watt technology | 1x Type-C input

Part No. 1001-0126













INDUCTIVE CHARGER WILINE 5 WIRELESS CHARGING FUNCTION

Wireless charger, compatible with all Qi-capable smartphones and Qi receivers 5 Watt technology | 1x Micro USB input Part No. 1001-0125





USB-C, USB-PD AND QUICK CHARGE

SUITABLE FOR LAPTOPS





POWER DELIVERY 60 WATT

High-speed USB charger for

1 USB and 1 Type-C port

Part No. 1001-0096

charging compatible devices.

2 PORTS





2 PORTS

POWER DELIVERY 45 WATT

High-speed USB charger for charging compatible devices. 1 USB and 1 Type-C port

Part No. 1001-0095

















USB CHARGER

1 PORT | TYPE-C

Intelligent USB charger 30 W compatible with Laptops, Apple MacBook Air, iPhone 12 & 13 and many more smartphones

Part No. 1001-0123













ADAPTER-SET

FOR LAPTOPS



USB-C LAPTOP ADAPTER-SET 8 DIFFERENT ADAPTERS

For laptops without USB-C connection 45 W / 60 W / 100 W USB-C PD power supplies and USB-C PD power banks



USB-CHARGERS FOR EVERYDAY USE

ANSMANN HOME CHARGER



USB-CHARGER 5 W | 1 PORT

Space-saving USB charger with one USB port for charging USB applications

Part No. 1001-0108 | 1001-0112*



USB-CHARGER 12 W | 2 PORTS

Ansmann USB charger with 2 USB ports for charging USB applications

Part No. 1001-0106 | 1001-0114*



USB-CHARGER

30 W | 4 PORTS

Ansmann USB charger with 4 USB ports for charging USB applications

Part No. 1001-0107 | 1001-0113*



USB-CHARGER

20 W | 2 PORTS | TYPE-C & A

High-speed USB charger with 1 USB and 1 USB Type-C port for charging Charging USB applications

Part No. 1001-0109 | 1001-0111*



USB-CHARGER

18 W | 1 PORT | QUALCOMM QC 3.0

High-speed USB charger for charging USB applications with Qualcomm Quick Charge 3.0

Part No. 1001-0099



USB-CHARGER

20 W | 1 PORT | TYPE-C

High-speed USB charger with 1 USB Type-C port perfect for the iPhone 12 - also for Android































CHARGING IN THE FAST LANE

FULL IN-CAR POWER

With the ANSMANN USB in-car charger you can charge any device even when driving. Up to 4 devices at the same time!

Or, why not try our new smartphone holders. Hold your device in your car with simple magnetic mounting.

CHARGE POWER 12W 18W 30W

Fast

SPECIAL FEATURES



You are always safe with us. If you have questions or problems with the product, you can rely on our manufacturer's guar-



With this USB charger you can charge your devices in any vehicle with 12 V DC.



Future-proof: With the new and flexible USB



Standard

New, freely available USB Type-C fast charging standard.

Ultra-fast



ULTRA-FAST CHARGING

You can charge your device at ultra-fast speed thanks to the quick-charge technology in our USB chargers.



Certified quick-charge function from Qualcomm.





USB CAR-CHARGER 5 W | 1 PORT

USB car charger with 1 USB port for charging **USB** applications

Part No. 1000-0031

∳ 5W



USB CAR-CHARGER

12 W | 2 PORTS

USB car charger with 2 USB ports for charging **USB** applications

Part No. 1000-0030









High-speed USB car charger with 1 ging Charging USB applications Part No. 1000-0032





USB CAR-CHARGER

30 W | 2 PORTS | TYPE-C & A

High-speed USB car charger with 1 USB and 1 USB Type-C port for char- USB and 1 USB Type-C port for charging Charging USB applications Part No. 1000-0029























2X2 USB CAR MOUNT WITH EXTENSION FOR REAR SEATS

Intelligent USB in-car charger 9.6 A with 4 USB ports and extension to the rear seats

Part No. 1000-0017



SMARTPHONE HOLDER FOR AIR VENT

Magnetic air vent holder for smartphones including 2 ultra-thin metal strips

Part No. 1700-0069



SMARTPHONE HOLDER FOR WINDSCREENS

Magnetic windscreen

holder for smartphones including 2 ultra-thin metal strips









LIGHTNING, MICRO-USB, USB TYPE-C

CHARGE CABLES FOR ALL DEVICES

The practical ANSMANN data and charge cables are ideal for charging as well as synchronising your data. The plug connectors are manufactured to the USB standard and so ensure a secure connection. Data is transferred flawlessly and end devices charged with maximum power.





STANDARD FFATURES

WITH ALL CHARGE CABLES



You are always safe with us. If you have questions or problems with the product, you can rely on our manufacturer's guar-



The head comprises a robust aluminium housing with high-quality strain relief.



Compatible with all common devices that have a Micro-USB, USB type-C or Lightning connector such as smartphones, tablets or



SYNCHRONISES ANY DEVICE

Any compatible device can synchronise images and data with our cables.





PROFESSIONAL ALL-ROUNDER,

ANSMANN MULTI-CABLES



bend protection. Fast charging. Up to 480 Mbit/s

Part No. 1700-0136



480 Mbit/s



2IN1 MICRO-USB TYPE-C

CHARGE AND DATA CABLE

Cable with USB Type-C and Micro-USB Aluminium housing with strain relief Fast charging | Up to 480 Mbit/s

Part No. 1700-0083



480 Mbit/s

TYPE-C **PROFESSIONAL**





CHARGE AND DATA CABLE

Power Delivery compatible Charging power up to 60 watts Fast charging | Up to 5 Gbit/s

Part No. 1700-0121 | 1700-0122*









Part No. 1700-0106 | 1700-0107*







*Front Part No. = 1.2 m Länge | Rear Part No. = 2.0 m length

MICRO, TYPE-C, LIGHTNING

ANSMANN STANDARD



MICRO-USB CHARGE AND DATA CABLE

Aluminium housing with strain relief Quick-charge compatible Data transfer up to 480 Mbit/s Compatible with common devices Part No. 1700-0076 | Art. no. 1700-0077*



LIGHTNINGCHARGE AND DATA CABLE

Aluminium housing with strain relief Quick-charge compatible Data transfer up to 480 Mbit/s Compatible with iPhone, iPod Part No. 1700-0078 | Art. no. 1700-0079*



TYPE-C USB 3.0 CHARGE AND DATA CABLE

Aluminium housing with strain relief Data transfer up to 5 Gbit/s Compatible with common devices

Part No. 1700-0080 | Art. no. 1700-0081*













*Front Part No. = 1.2m Länge | Rear Part No. = 2.0m length

480



MICRO, TYPE-C, LIGHTNING

ANSMANN BASICS



MICRO-USB

CHARGE AND DATA CABLE

Welded plastic housing Fast charging | Up to 480 Mbit/s Compatible with common devices

Part No. 1700-0129





LIGHTNINGCHARGE AND DATA CABLE

Welded plastic housing Fast charging | Up to 480 Mbit/s Compatible with iPhone, iPad, iPod

Part No. 1700-0131







TYPE-C CHARGE AND DATA CABLE

Welded plastic housing Data transmission with up to 480 Mbit/s Compatible with common devices







FLEXIBLE POINT OF SALE OPTIONS

ANSMANN DISPLAY CONCEPTS

SIMPLE, MODERN, INDIVIDUAL



THE ALLROUNDER

POWERBANKS
USB-CHARGERS &
CABLES

Many other presentation aids available on request

Can be tailored to individual needs!

ANSMANN AG

Industriestr. 10 97959 Assamstadt Germany

Phone: +49 (0) 6294 4204-0 E-Mail: info@ansmann.de

Photos: ANSMANN AG
Marco Schoppa
Kevin Bailey
Unsplash
iStock

Subject to technical changes. We assume no liability for errors and printing errors.

All brand names are the property of their respective owners.

Part No. 0010-0166 • 03/2022



ANSMANN UK LTD.

Units 11-12, R024 Harlow Business Park Harlow, Essex, CM19 5QB <u>United Kingdom</u>

Phone: +44 (0) 870 609 2233 E-Mail: uk@ansmann.de

ANSMANN ENERGY FRANCE

5, Place Copernic, Immeuble Boréal - Courcouronnes F-91023 Evry Cedex Paris, France

Phone: +33 (1) 60791479 E-Mail: france@ansmann.de

ANSMANN ELECTRONICS CO. LTD.

Da Lian Industrial Park, Rengtu, Ruhu Town Huicheng District, Huizhou City, Guangdong, China Postal Code: 516169 China

Phone: +86 752 6276688 E-Mail: china@ansmann.de

ANSMANN NORDIC AB

Postbox 17006 16717 Bromma Sweden

Phone: +46 (0) 31 47 32 00 E-Mail: nordic@ansmann.de

ANSMANN ENERGY INTERNATIONAL LTD.

Unit 3117-18, 31/F,
Tower 1, Millennium City 1,
No. 388 Kwun Tong Road,
Kwun Tong, Kowloon, Hong Kong
Phone: +852 2877 8233
E-Mail: hongkong@ansmann.de

ANSMANN TRADING COMPANY LTD.

Da Lian Industrial Park, Rengtu, Ruhu Town Huicheng District, Huizhou City, Guangdong, China Postal Code: 516169 China

Phone: +86 752 6276688 E-Mail: china@ansmann.de