



Product data sheet

Power tools for trade & industry

Cordless Angle Grinder

PRO GWS 18V-11



All-round performer for maximum cutting and grinding versatility.

The most important data

Battery voltage	18.0 V
No-load speed	9,000 rpm
Disc diameter	115 mm

Order number 0 601 9N4 101

Technical data

Additional data

Battery voltage	18.0 V
No-load speed	9,000 rpm
Disc diameter	115 mm
Grinding spindle thread	M14
Bore size, diameter	22.23 mm
Weight excl. battery	1.7 kg
X-LOCK	No
BITURBO	No

Noise/vibration information

Surface grinding (roughing)

Uncertainty K	1.5 m/s ²
---------------	----------------------

Sanding with sanding sheet

Uncertainty K	1.5 m/s ²
---------------	----------------------



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Versatile all-rounder with balanced design for wide range of applications
- Excellent durability thanks to 1100W of power with optimized overload capacity
- More comfort and less fatigue assured by anti-vibration handle and slimmer grip
- Lower risk of injury while you work thanks to full suite of safety features



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/jo/en/wac/>

