
596 direct reading torque wrenches for right-hand and left-hand tightening torque accuracy: ±4%

UNI EN ISO 6789

A signal light and an intermittent sound mean the pre-set torque load is achieved.

Nm
Kgfm
lbf.ft
■
A
mm
L
mm
kg





	art.	Nm	Kgfm	lbf.ft	■	A mm	L mm	kg	
005960010	596/40SL	80÷400	8÷40	60÷300	3/4	111	710	3,2	10
005960020	596/80SL	160÷800	16÷80	120÷600	3/4"	115	1025	4,85	20