

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0151350603
Status: Active
Overview: CLIK-Mate™ Wire-to-Board Connectors
Description: CLIK-Mate™-to-CLIK-Mate™ Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 6 Circuits, Beige

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable Assemblies
Series 15135
Assembly Configuration Dual Ended Connectors
Connector to Connector CLIK-Mate™-to-CLIK-Mate™
Overview CLIK-Mate™ Wire-to-Board Connectors
Product Literature Order No 987651-6143
Product Name CLIK-Mate™ OTS
UPC 191128160339

Physical

Cable Length 300.00mm
Circuits (Loaded) 6
Color - Resin Beige
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin PBT
Net Weight 6.544/g
Packaging Type Bag
Pitch - Mating Interface 1.50mm
Plating min - Mating 0.406µm
Plating min - Termination 0.406µm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.10mm
Wire Size AWG 24
Wire/Cable Type UL 1061

Electrical

Current - Maximum per Contact 1.5A
Voltage - Maximum 100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing 2012341677-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

15135 Series

Mates With

503395 Bottom-Entry Receptacle . 503175
Right Angle, Through Hole Receptacle .
502585 Right Angle, Surface Mount
Receptacle
 503159 Vertical, Through
Hole Receptacle
 502584 , 505405
Vertical, Surface Mount Receptacle