



Body protection

SAKOYAOR

RAIN

Windproof rain jacket, fleece lining for medium warmth, reflective and fluorescent inserts for better visibility



Specific benefits

Comfort

- Fleece lining for soft warmth
- Stretch fabric for freedom of movement
- Lightweight clothing for greater comfort

Performance

- Waterproof fabric to stay dry in medium rain

Visibility

- Retro-reflective strip for night-time visibility

Technologies & labels

- Segmented strip



Recycled polyester

Applications

- Agriculture
- Fishing
- Building
- Finishing works / Craftsmanship
- Transportation
- Storage

Certifications and norms

 CATEGORY 2

 EN343
4
3
X

 EN 17353
TYPE AB3

EN ISO 13688

Protects against risks



High vis



Weather



Body protection

SAKOYAOR

RAIN

Windproof rain jacket, fleece lining for medium warmth, reflective and fluorescent inserts for better visibility

Standards - Details



EN343 PROTECTIVE CLOTHING AGAINST RAIN

4 RESISTANCE CLASS OF THE PENETRATION OF WATER (1 TO 4) WP
3 EVAPORATIVE RESISTANCE CLASS (1 TO 4) RET
X READYMADE GARMENT RAIN TOWER (OPTIONAL)

Technical details

Collection	All year round
Type of workwear	Waterproof jacket
Gender	Mixte
Size range	S → 3XL
Workwear color	Black, Grey, Orange
Seams	Waterproof
Support material details	Twill - 100% recycled polyester - pu-membrane Lining - 100% recycled polyester fleece
Total product weight (g/m ²)	315
Hood type	Fixed hood
Fastening	Zipper fastening
Lower sleeve	Elastic
Lower body	Bottom drawstring
Number of exterior pockets	3
External pockets	3 zipped pockets
Number of inside pockets	2
Inner pockets	1 zip inner pocket, 1 phone inner pocket
Access to marking by inside zip	yes
Marking type	Screen printing, Transfer printing
Waterproof zipper	yes
Elastic	Wrist
Reflective segmented tapes	yes








SAKOYAOR

RAIN

Protective clothing

Windproof rain jacket, fleece lining for medium warmth, reflective and fluorescent inserts for better visibility

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
SAKOJALV02BK OSM [SAKOYNOPT]	Black-Orange	S	SAKOYAOR	3295249310547	13295249310544	10	1	8.0 kg	65.0 cm	40.0 cm	30.0 cm
SAKOJALV02BK OMD [SAKOYNOTM]	Black-Orange	M	SAKOYAOR	3295249310813	13295249310810	10	1	8.0 kg	65.0 cm	40.0 cm	30.0 cm
SAKOJALV02BK OLG [SAKOYNOGT]	Black-Orange	L	SAKOYAOR	3295249310820	13295249310827	10	1	8.0 kg	65.0 cm	40.0 cm	30.0 cm
SAKOJALV02BK OXL [SAKOYNOXG]	Black-Orange	XL	SAKOYAOR	3295249310837	13295249310834	10	1	8.0 kg	65.0 cm	40.0 cm	30.0 cm
SAKOJALV02BK O2X [SAKOYNOXX]	Black-Orange	XXL	SAKOYAOR	3295249310844	13295249310841	10	1	8.0 kg	65.0 cm	40.0 cm	30.0 cm
SAKOJALV02BK O3X [SAKOYNO3X]	Black-Orange	3XL	SAKOYAOR	3295249310851	13295249310858	10	1	8.0 kg	65.0 cm	40.0 cm	30.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height