

Angle Drill 18V LXT



DDA351RMJ

Voltage:	18v
Max. in wood:	25mm
Max. in steel:	10mm
No Load Speed:	0 - 1800rpm
Max Torque:	13.7Nm
Battery Type:	Lithium-ion
Battery Quantity (3.0 Ah):	0
Vibration: Drilling:	2.5m/sec ²
Vibration K factor:	1.5m/sec ²
Noise sound pressure:	73dB(A)
Noise K factor:	3dB(A)
Net weight:	1.6 - 1.9kg
Battery quantity (4.0Ah):	2



- Keyless chuck.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- 4 pole motor.
- Conveniently located push button for forward and reverse.
- High comfort grips.
- Large trigger.
- LED job light with afterglow.