

Rittal – The System.

Faster – better – worldwide.

► Catalog 33
North American Edition 2012

50

Rittal. Power and Vision!

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP



System accessories Page 531

Material:

Carbon steel
Enclosure: 14 ga (2 mm)
Door: 14 ga (2 mm)

Surface finish:

Enclosure and door:
Dipcoat primed, powder-coated
textured RAL 7035 (light grey)

Configuration:

Hinged screw cover,
foamed-in-place gasketing,
control panel slants 30 or 60°

Protection rating:

UL Type 12/13
UL/cUL
UL file #: 118617

Depth: 7 - 9" (180 - 231 mm), Height: 8 - 12" (203 - 305 mm)

Height (H1) inches (mm)	PU	8 (203)	8 (203)	8 (203)	8 (203)	12 (305)	12 (305)	Page
Width (B1) inches (mm)		8 (203)	12 (305)	16 (406)	20 (508)	12 (305)	16 (406)	
Depth (T1) inches (mm)		7 (180)	7 (180)	7 (180)	7 (180)	9 (231)	9 (231)	
Part No.	1	C080807HC	C081207HC	C081607HC	C082007HC	C121209HC	C121609HC	
Weight lb (kg)		8 (3.5)	10 (4.7)	13 (5.8)	15 (7.0)	14 (6.5)	18 (8.0)	

Accessories

Base inches (mm)	18 x 18 x 1 (457 x 457 x 25)	1	C18SBASEC					145
Column inches (mm)	4 x 4 x 35 (102 x 102 x 889)	1	C44SCOLC					145

Depth: 9 - 11" (231 - 282 mm), Height: 12 - 16" (305 - 406 mm)

Height (H1) inches (mm)	PU	12 (305)	12 (305)	16 (406)	16 (406)	16 (406)	
Width (B1) inches (mm)		20 (508)	24 (610)	16 (406)	20 (508)	24 (610)	
Depth (T1) inches (mm)		9 (231)	9 (231)	11 (282)	11 (282)	11 (282)	
Part No.	1	C122009HC	C122409HC	C161611HC	C162011HC	C162411HC	
Weight lb (kg)		21 (9.6)	24 (11.1)	23 (10.4)	27 (12.3)	32 (14.3)	

Accessories

Base inches (mm)	18 x 18 x 1 (457 x 457 x 25)	1	C18SBASEC	-	C18SBASEC	-	145
	24 x 24 x 1 (610 x 610 x 25)	1	-	C24SBASEC	-	C24SBASEC	145
Column inches (mm)	4 x 4 x 35 (102 x 102 x 889)	1	C44SCOLC	-	C44SCOLC	-	145
	6 x 6 x 35 (152 x 152 x 889)	1	-	C66SCOLC	-	C66SCOLC	145

Depth: 11 - 13" (282 - 332 mm), Height: 16 - 20" (406 - 508 mm)

Height (H1) inches (mm)	PU	16 (406)	16 (406)	20 (508)	20 (508)	20 (508)	
Width (B1) inches (mm)		30 (762)	36 (914)	20 (508)	24 (610)	30 (762)	
Depth (T1) inches (mm)		11 (282)	11 (282)	13 (332)	13 (332)	13 (332)	
Part No.	1	C163011HC	C163611HC	C202013HC	C202413HC	C203013HC	
Weight lb (kg)		38 (17.0)	44 (19.9)	34 (15.2)	39 (17.5)	46 (20.9)	

Accessories

Base inches (mm)	24 x 24 x 1 (610 x 610 x 25)	1	C24SBASEC					145
Column inches (mm)	6 x 6 x 35 (152 x 152 x 889)	1	C66SCOLC					145