

Set of cable gland + nut stainless steel M25 AISI316L, IP68, UL approved

NSYCGX25H

EAN Code: 3606481360304

Price: 49,55 EUR

Main

Range	PanelSeT	
Product or component type	Cable gland	
Accessory / separate part category	Cable management accessory	
Range compatibility	PanelSeT PanelSeT CRN PanelSeT PanelSeT S3D PanelSeT PanelSeT S3X	
Mounting location	Enclosure top Enclosure bottom	
Cable entry	Cable gland M25	
Device composition	1 cable gland 1 lock nut 1 seal	
Quantity per set	Set of 4	
Material	Seal: CR (chloroprene) Body: stainless steel AISI 316L	

Complementary

Colour	Grey
Fixing mode	Screwed By nut
Height	35.5 mm
Net weight	0.041 kg

Environment

Product certifications	VDE
Flame retardance	V2 conforming to UL 94
Ambient air temperature for operation	-20100 °C permanent -40150 °C intermittent
IP degree of protection	IP68 conforming to IEC 60529 5 bar, 30 min

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	3.000 cm

Rates duty January 2016

Package 1 Length	15.000 cm
Package 1 Weight	50.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	4.000 cm
Package 2 Width	6.000 cm
Package 2 Length	15.000 cm
Package 2 Weight	200.000 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Take-back

Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
Use Again		
○ Repack and remanufacture		

No