

HT340R and HT180

HT340R

Powered by Rechargeable



- HT340R is a rechargeable Li-ion headtorch
- 340 Lumens light output delivering 200m beam
- Proximity distance dimming function for close up work
- 3 Light modes: spot, wide beam and distance dimming
- Adjustable non-slip head straps
- Rechargeable via USB cable

Recharges via Micro USB




Supplied with:
USB charging cable
Headstrap

Specifications HT340R

Light Output	340 lumens
Beam distance	200 Metre Beam
Battery	Li-ion
Runtime	1hrs 42mins high 130hrs low
Light Settings	Spot, wide and distance dimming
Dimensions	(L) 62mm (D) 44mm (H)45.6mm
Product Weight	100g Product weight including battery
Boxed Weight	150g
Boxed Size	(L) 144mm (D) 60mm (H)230mm
IP Rating	IP66
Part No.	NSHT340R

HT180

Powered by 3x



- The HT180 delivers 180 lumens light output and delivers a 100m beam
- Proximity distance dimming function for close up work
- 3 Light modes: spot, wide beam and distance dimming
- Adjustable non-slip head straps
- Supplied with 3 x AAA Alkaline batteries and headstrap

Supplied with:
AAA Alkaline batteries
Headstrap

Specifications HT180

Light Output	180 lumens
Beam distance	100 Metre Beam
Battery	3 x AAA Alkaline Batteries
Runtime	3hrs high 130hrs low
Light Settings	Spot, wide and distance dimming
Dimensions	(L) 62mm (D) 44mm (H)45.6mm
Product Weight	100g Product weight including battery
Boxed Weight	150g
Boxed Size	(L) 144mm (D) 60mm (H)230mm
IP Rating	IP66
Part No.	NSHT180