




其他视图



## SCHROFF

### 19" AC/DC 开关电源, maxpower 100 W, 单相

产品目录号: 13100-102

- 有源均流母线 (CSB)
- 宽输入电压范围90 ...254 VAC和100 ...360 VDC, 带有源功率因素校正 (PFC)
- 发出信号: 输出电压正常
- 用于冗余运行的集成解耦二极管
- 单输入电压
- 高功率密度



## 说明

### 备注:

请分别订购前面板

### 应用:

兼容19"

### 规格:

通用型19"

### 输出电压:

1

### 备注:

主电源电压>190 VAC时的输出数据:  $T_a = 0 \dots 50 \text{ } ^\circ\text{C}$  5 V / 16 A

### 类型:

开关PSU

### 功率类型:

AC/DC

### 输出功率:

100 ... 180 W

### 交付包括:

商品	数量	说明
1	1	兼容19"的电源, 高3 U, 宽度A: 6 HP, 深171.93 mm (板深160 mm), 连接器H 15 M, 编码条 (已安装)



## 技术数据

---

产品目录号 [13100-102](#)

电压1 V 5.0  
 电流1 A 16.0  
 功率W 80.0  
 高度U 3  
 宽度HP 6

## 技术数据

Connector pin-out	Connection
-----	-----
Pin 4	Output + V1
Pin 6	Output + V1
Pin 8	Sense line + V1
Pin 10	Sense line V0 V1
Pin 12	Output 0V V1
Pin 14	Output 0V V1
Pin 16	-
Pin 18	-
Pin 20	-
Pin 22	CSB
Pin 24	Output OK
Pin 26	-
Pin 28	L
Pin 30	N
Pin 32	PE

## 文档

---



Main Catalog - Power supply systems (ROW)



Declaration of conformity



Safety instructions



UL



Operating instructions



How is the current share bus (CSB) connected?



CB-test certificate



How does the signal output o.k. work?

## 链接

---



Configurator - Power Supplies Units

## 附件

商品		
	不锈钢EMC垫片, 3 U, 97 mm, 不锈钢, 每个前面板只需2件, PU 10件	21101-705
	编码, PU (1个编码条, 2个编码销)	60800-123