

Datasheet

RS Pro Straight 75Ω Cable Mount BNC Connector Plug, Crimp Termination PSF 1/3 Nickel

RS Stock No: **546-3715**



Product Details

RS Pro straight cable mount BNC connector plug features a crimp ferrule, nickel plated body, gold plated centre contact and is for use with a variety of RF coaxial cable types. This male connector plug has 75 Ω impedance. It operates at a voltage rating of 335 V and temperature rating of -65 to +85°C. This connector plug is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Brass construction with nickel and gold plated contacts
- Crimp termination method
- Male connector
- RS BNC connectors are suitable for a variety of applications including video signalling and test equipment

Specifications:

Body Orientation	Straight
Body Plating	Nickel
Cable Type	PSF 1/3
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	75 Ω
Mounting Type	Cable Mount
Polarity	Normal
Termination Method	Crimp
Standards Met	RoHS Compliant