

## Features

- High current accuracy
- Protection against excessive temperature
- Snap action
- Automatic reset type
- Long life
- P.B.T resin enclosure
- Reliable

## RS PRO Thermal Circuit Breaker

RS Stock No.: 774-0083, 774-0077, 774-0095,  
744-0099, 774-0106, 774-0109, 774-1112,  
774-1118



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

These compact automatic reset overcurrent protectors are designed to protect audio speaker systems, amplifiers and power supplied from internal overcurrents. Available up to 6 amps. PC mounting.

## General Specifications

Circuit Breaker Type	Thermal Magnetic
Mounting type	PC Mounting

## Mechanical Specifications

Enclosure material	PBT resin
--------------------	-----------

## Electrical Specifications

Rated Hold Current (AC at 25°C)	See table below
Max Voltage (at 25°C)	250V AC
Trip Time 200% overload current	Within 30 seconds
Trip Time 300% overload current	Within 5 seconds

## Approvals

Standards Met	RoHS
---------------	------

## Similar Products

Stock No.	Rated Hold Current (A) AC @25°C	Internal Resistance (mΩ)	Max Voltage (V) AC @25°C	Maximum Interrupt Current (A)
774-0077	1.0	<150	250	20
774-0083	1.6	<100	250	20
774-0095	1.9	<75	250	20
774-0099	2.2	<75	250	20
774-0109	2.5	<75	250	25
774-0106	3.0	<35	250	30
774-0118	5.0	<30	250	50
774-0112	6.0	<30	250	60

### Operating Sequence

