

TU, Polyurethane Tubing, Metric Size

TU0604Y1-20

Datasheet

Series TU tubing represents a new high quality standard in metric size polyurethane tubing. Series TUH, hard polyurethane tubing, is available in a standard or high pressure type and TUS is a soft polyurethane tubing.

Size	0604 (O.D. Ø6 I.D. Ø4)
Color	Y1 (Yellow, Solid)
Roll Length	20 m
Reel Length	None
Suffix	None
Pressure medium	Air, Water
Maximum ambient temperature	60 °C / 40 °C for Water
Minimum ambient temperature	-20 °C (with no freezing) / 0 °C for Water
Number of pneumatic connections	2 pcs.
Max. operating pressure at 20 °C	0.8 MPa
Weight	0.380 Kg

Dimensions

Additional information

Catalogue

[TU-29COLOR-A_EU.pdf](#)